



# PRODUCT SPECIFICATION


## 3.8" ACM High Temperature Turboclean RO Element

Model	Permeate flow GPD (m3/day)*	Average Salt Rejection (%)	Minimum Salt Rejection (%)
3840-M2D7U8	1,750 (6.0)	99.50	98.50

Performance is based on the following test conditions: 2,000.0 ppm NaCl, 225.0 psi, 25°C, 15% recovery, pH 8.0, 30 minutes operation.

### OPERATIONAL AND DESIGN DATA

Membrane Type.....	ACM Fully Aromatic Polyamide Advanced Composite Membrane
Configuration.....	Spiral Wound, Turboclean Shell
Active Membrane Area.....	70 ft <sup>2</sup> (6.4 m <sup>2</sup> )
Recommended Applied Pressure.....	100 - 300 psi (7 - 21 bar)
Maximum Applied Pressure.....	600 psi (41 bar)
Recommended Operating Temperature.....	35 - 140°F (2 - 60°C)
Feedwater pH Range.....	2 - 11 continuous
Chlorine Tolerance.....	<0.1 ppm
Maximum Feed Flow.....	20 GPM (4.5 m3/hr)
Minimum Brine Flow/Permeate Flow Ratio....	5:1
Maximum SDI ( 15 minutes) .....	5.0
Maximum Turbidity.....	1 NTU
Application.....	Whey Concentration



Element Weight : 12 (5.4)  
 Length (A) : 38.8 (984)      Diameter (B) : 3.8 (96)      Permeate Tube (C) : 0.83 (21.2)  
 Units in pounds and inches, units in paranthesis in kilograms and millimetres.  
 Mechanical Configuration: Sanitary Style Core Tube  
 Feed Spacer: 0.031" thick diamond spacer

\* Permeate flow is clean water flux at standard conditions above. Not applicable for all feedwater conditions. Individual element's permeate flow may vary +/- 15%.



**Engineered Membrane**  
**SOLUTIONS**